

BEG 1000 B



This dispersion system can generate high mass flows continuously, e.g., 6 kg/h, with optimal dosing constancy.

BENEFITS

- Excellent short-term and long-term dosing constancy
- Easy to operate
- Quick and easy to clean
- Remote control or computer-controlled
- Pulse mode
- Easy to fill while in operation
- Large reservoir (1,500 cm³)
- Robust design, proven in industrial applications

- Reliable function
- Reduces your operating expenses
- Low maintenance

APPLICATIONS

- Filter industry: Loading test of
 - Engine filters as per ISO 5011
 - Hot gas filters
 - Bag filters
 - Air filters
 - Cyclones
- Chemical and pharmaceutical industry
- Cement industry

DATASHEET

Particle size range	0.1 – 200 μm	Maximum particle number concentration	Ca. 10^7 particles/ cm^3
Volume flow	80 – 165 Nl/min	Mass flow (particles)	Type B: 100 – 6,000 g/h (with reference to SAE Fine, A2 dust)
Filling quantity	500 g	Power supply	115 – 230 V, 50/60 Hz
Particle material	Non-cohesive powders and bulks	Dosing time	Several hours nonstop
Pre-pressure	4 – 8 bar	Carrier/dispersion gas	Random (generally air)
Compressed connection	air Quick coupling	Aerosol outlet connection	Type B: $\varnothing_{\text{inside}} = 8 \text{ mm}$, $\varnothing_{\text{outside}} = 12 \text{ mm}$
Reservoir volume	1,500 cm^3	Dimensions	Dosiereinheit: 610 • 260 • 340 mm (H • B • T), Steuereinheit: 195 • 260 • 340 mm (H • B • T)